



Product technical data sheet

LABOR 100 ECT-F

Cod. LAB0101

General features



Temperature range	Adjustable +2°C / +15 °C
Factory setpoint Increment	+5°C 0.1°C
Ambient working class Climatic class	From +16°C to +38°C N-ST
Nominal capacity	100 lt (3,53 cu ft)

External dimensions (WxDxH) 52x63,5x71 cm Internal dimensions (WxDxH) 44x51,6x42,1 cm

Net weight without any internal 46 kg fittings

Package dimensions | Weight

Gross capacity | Net capacity

Cardboard on pallet 55x69x87 cm | weight 55 kg

126 lt (4,45 cu ft) | 96 lt (3,40 cu ft)

Wooden crate on pallet 60x77x103 cm | weight 64,5 kg

Structure

Lightning

Internal fittings

Monocoque type, made of plasticized, non-toxic white steel interior/exterior, coated with a special antibacterial-type film, or in inner 18/10 Aisi 304 stainless steel. Rounded corners and tray-type

High-density (43 kg/m³), in-walls injected PUF, without any CFC, Insulation type water-foam based.

Insulation thickness 40 mm

Feet No.4 adjustable small feet

No.1 solid door with ergonomic handle, self-closing thanks to the Door spring hinge and 90° stop position.

Full LED, all length of inner chamber, automatic switching on at

door opening.

Customizable and height adjustable, it can mix independently:

wire shelves supported by adjustable clips (dim.cm.40x49)

fully extractible drawers made of aluminium, with dividers (WxDxH): cm 10x45x7,5 (nr 3 compartments)

fully extractible drawers made of aluminium, without dividers (WxDxH): cm 33x45x7,5

Suggested internal fittings No. 1 wire shelf

Refrigeration system

Refrigeration	Professional, ventilated, forced, hermetic compressor type
Defrost	Automatic, adaptive, including condensate water vaporisation
Refrigerant	Natural R290
GWP ODP	3 0



Disclaimer: Images are purely indicative. The features and the accessories of the products may differ according to model and application.

Electronic controller



Alarm system

Controller Controller ECT-F control®

Type of controller Electronic controller, back-lit alphanumeric LCD display and

resolution 0,1°C

Power switch Integrated in user's interface

Security features Settable user password

Visual and acoustic for temperature alarms and failures such as:

Open door

High temperature

· High temperature caused by power failure.

Low temperature

· Power failure (when the energy returns, only in event of High

Temperature) Clogged condenser

· Any functional failure/faulty parts

Data and event recordingsLast 12 events available on the displaySettable temperature alarm limitsYes, through parameter adjustment

Control sensors NTC type probes

Electrical and functional data

Standard power supply 230V / 1ph / 50Hz

Standard plug type Schuko type "G"

Compressor protection Overload Protector included

Power absorption/current kW 0,14 (Amp 0,9)

Inrush current Amp 2,5
Noise level <40 dBA

Heat emission according to EN 12900 W 20

Hold over time at 20°C ambient (air) 3,8 h (from +5°C to +15°C)

Energy consumption at 20°C ambient 0,5 kWh/24h

Conformity

Directive 2006/42/EC (Machine directive)

Directive 2011/65/EC (ROHS II) Directive 2015/863/ EC (ROHS III) Directive 2012/19/EC (RAEE)

Directives and regulations

Directive 2012/19/EC (RAEE)

Directive 2014/30/EC (EMC)

Directive 2014/35/EC (LVD)

Regulation (EU) 517-2014 (F-gas) Regulation (EU) 1907-2006_REACH

Available certificate CE

Application environment

Non-flammable, non-explosive, non-corrosive, with adequate air

exchange

Accessories available on request

	Accessories available on request
Lock with key	
DMLP Digital Monitor®	Alarm and temperature recording system completely independent from the ECT-F control® controller, equipped with buffer battery and featuring an additional backlit, alphanumerical LCD display. DMLP Digital Monitor provides: • Temperature and alarms data recording on extractible SD card covering the last 5 years, with one minute sampling frequency. • Back-up buffer battery granting alarms and recording during power cut. The life of the battery is approximately 12 hours during power failures. • Pre-set for alarms remoting (dry contact) The SD can be inserted in any pc using a card-reader and includes a freely supplied software, Capture, allowing to download, save and print any data. Information can be arranged as a graph or tabular forms, both fully customizable.
DMLP Printer	
ECT-F PLUS controller	Evolution of ECT-F control® controller, including following additional features: Backup batteries for power failure alarm, up to 48 Hrs Min and Max temperature log, manually resettable High temperature alarm during power failure Refrigerator temperature visible even during power failure Alarm contact available on control board, remotable Additional programmable relays output available
Additional wire shelf kit	Please refer to model LABOR 100 ECF1 PLOS
Extractible drawer on telescopic slides	
Extractible drawer without inner dividers on telescopic slides	
Plexiglas front panel for extractible drawer	
Castors kit with brakes	
One-way small castors	
Inner socket (no.1)	
35mm access port with stopper (no.1)	
Port hole mm 15 (no.1)	
No.1 humidity sensor	
No.1 PTI00 sensor with free contacts	
Non-standard plug and cable	
Power 220V/60Hz	
Power 115V/60Hz	
Mains voltage stabilizer	
Wooden crate package	