Model BF 720 | Standard-Incubators with forced convection

The BINDER incubator of the BF Avantgarde.Line series with forced convection is suitable for all gentle incubation applications, particularly under a full load and large batch throughputs. This incubator is extremely homogeneous and has quick recovery times.

BENEFITS

- Excellent temporal and spatial temperature accuracy
- High process reliability
- 100°C disinfection routine



Model 720

IMPORTANT FEATURES

- Temperature range: +10°C above ambient temperature to +100°C
- High temperature accuracy thanks to APT.line™ technology
- Forced convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap
- Inner door made of tempered safety glass

- 2 chrome-plated racks
- 4 stable castors, two with brakes, from 720 liters
- Class 3.1 integrated independent temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

Interior volume [L]	Power supply - unit fuse	Plug*	Version	Model version	ArtNo.
Model BF 720					
	230 V 1~ 50/60 Hz -	CEE 7/7	Standard	BF720-230V	9010-0321
734	240 V 1~ 60 Hz -	NEMA 6-20	Standard	BF720UL-240V	9010-0322



TECHNICAL DATA

Data


Data		
Designation	BF720-230V	BF720UL-240V
Article Number	9010-0321	9010-0322
Option model	Standard	Standard
Performance Data Temperature		
Temperature range	+10 °C above ambient temperature to 100 °C	+10 °C above ambient temperature to 100 °C
Temperature uniformity at 37°C	0.3 ± K	0.3 ± K
Temperature uniformity at 100°C	1.6 ± K	1.6 ± K
Temperature fluctuation at 37°C	0.1 ± K	0.1 ± K
Temperature fluctuation at 100°C	0.2 ± K	0.2 ± K
Heating up time to 100°C	45 min	45 min
Heating up time to 37°C	15 min	15 min
Recovery time after door was opened for 30 s at 37°C	4 min	4 min
Electrical data		
Rated Voltage	230 V	240 V
Power frequency	50/60 Hz	60 Hz
Nominal power	1,75 kW	1,85 kW
Phase (Nominal voltage)	1~	1~
Dimensions and weights		
Interior volume	734 L	734 L
Net weight of the unit (empty)	166 kg	166 kg
Load per rack	45 kg	45 kg
Permitted load	315 kg	315 kg
Wall clearance back	160 mm	160 mm
Wall clearance sidewise	100 mm	100 mm
Housing dimensions not incl. fittings and connections		
Width net	1,165 mm	1,165 mm
Height net	1,590 mm	1,590 mm
Depth net	870 mm	870 mm
Internal Dimensions		



Interior width1,000 mm1,000 mmInterior height1,300 mm1,300 mmInterior depth565 mm565 mmInner doors22Unit doors22Unit doors22Environment-specific data43 dB(A)43 dB(A)Energy consumption at 10°°C580 Wh/h580 Wh/hEnergy consumption at 37°C130 Wh/h130 Wh/hFxtures130 Wh/h2/16			
Interior depth\$65 mm\$65 mmInner doors22Unit doors22Frvironment-specific data2Sound-pressure level43 dB(Å)43 dB(Å)Energy consumption at 100°C\$80 Wh/h\$80 Wh/hEnergy consumption at 37°C130 Wh/h130 Wh/h	Interior width	1,000 mm	1,000 mm
Inner doors22Unit doors22Environment-specific data3Sound-pressure level43 dB(A)43 dB(A)Energy consumption at 100°C580 Wh/h580 Wh/hEnergy consumption at 37°C130 Wh/h130 Wh/hFixtures	Interior height	1,300 mm	1,300 mm
Unit doors22Environment-specific data43 dB(A)43 dB(A)Sound-pressure level43 dB(A)43 dB(A)Energy consumption at 100°C580 Wh/h580 Wh/hEnergy consumption at 37°C130 Wh/h130 Wh/hFixtures	Interior depth	565 mm	565 mm
Environment-specific data Sound-pressure level 43 dB(A) 43 dB(A) Energy consumption at 100°C 580 Wh/h 580 Wh/h Energy consumption at 37°C 130 Wh/h 130 Wh/h Fixtures 580 Wh/h 580 Wh/h	Inner doors	2	2
Sound-pressure level43 dB(Å)43 dB(Å)Energy consumption at 100°C580 Wh/h580 Wh/hEnergy consumption at 37°C130 Wh/h130 Wh/hFixtures	Unit doors	2	2
Energy consumption at 100°C 580 Wh/h 580 Wh/h Energy consumption at 37°C 130 Wh/h 130 Wh/h	Environment-specific data		
Energy consumption at 37°C 130 Wh/h Fixtures	Sound-pressure level	43 dB(A)	43 dB(A)
Fixtures	Energy consumption at 100°C	580 Wh/h	580 Wh/h
	Energy consumption at 37°C	130 Wh/h	130 Wh/h
Number of shelves (std./max.) 2/16 2/16	Fixtures		
	Number of shelves (std./max.)	2/16	2/16

All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

DIMENSIONS Incl. fittings and connections [mm]



OPTIONS

Designation	Description	BF 720	*	ArtNo.
	left			
	10 mm	•	01	8012-1274
	30 mm	•	01	8012-1156
Access port with silicone plug	50 mm	•	01	8012-1164
	right			
	10 mm	•	01	8012-1267
	30 mm	•	01	8012-1153
	50 mm	•	01	8012-1162

BINDER Best conditions for your success

Designation	Description	BF 720	*	ArtNo.
	top			
	10 mm	•	01	8012-1261
	30 mm	•	01	8012-1150
	50 mm	•	01	8012-1159
	100 mm	•	01	8012-1166
Alarm function for overheating	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device	•	-	8012-1634
Analog output 4-20 mA	for temperature values (output not adjustable)	•	02	8012-1622
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	•	-	8012-1111
Calibration certificate, temperature	for temperature, measurement in center of chamber at specified temperature	•	-	8012-1130
	temperature measurement incl. certificate, 9 measuring points at specified temperature	•	-	8012-1548
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	•	-	8012-1569
	temperature measurement incl. certificate and 27 measuring points at specified temperature	•	-	8012-1590
Clock	battery-backed	•	-	8012-1639
Door lock	lockable door handle	•	-	8012-1816
Ethernet interface	for Multi Management Software APT-COM TM	•	-	8012-0991
nner chamber, reinforced	max. total load 350 kg	•	-	8012-1829
t 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	•	-	8012-1618

ACCESSORIES

Designation	Description	BF 720	*	ArtNo.
	for simple logging and documentation requirements with up to 5 networked units.			
APT-COM™ 4 BASIC-Edition	version 4, BASIC edition	•	-	9053-0039
APT-COM™ 4 GLP-Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper- proof way in line with the requirements of FDA Regulation 21 CFR 11.			
	version 4, GLP edition	•	-	9053-0042
APT-COM™ 4 PROFESSIONAL-	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.			
Edition	version 4, PROFESSIONAL edition	•	-	9053-0040
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	•	-	8012-2250

BINDER Best conditions for your success

Designation	Description	BF 720	*	ArtNo.
	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature, CO_2 , O_2 – or pressure, depending on unit			
Qualification documents	– Digital in PDF format	•	-	7057-0005
	Hard copy inside folder	•	-	7007-0005
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature, CO ₂ , O ₂ , pressure, depending on unit			
	– Digital in PDF format	•	-	7057-0001
	– Hard copy inside folder	•	-	7007-0001
Rack	max. load per rack 45 kg			
	chrome plated	•	-	8012-2044
	stainless steel	•	-	8012-2170
	max. load per rack 70 kg			
Rack, heavy load	Stainless steel	•	-	8012-2185
half parforated	max. load per rack 40 kg			
Shelf, perforated	Stainless steel	•	-	8012-2178

SERVICES

Designation	Description	*	ArtNo.
Calibration services			
	Calibration of one (1) test temperature specified by the user in center of chamber, including certificate	-	DL30-0120
Calibration certificate, temperature	Extension of calibration of one (1) additional test temperature specified by the user in the center of the usable space, including certificate	-	DL30-0102
Temperature measurement, 9 measuring points	Temperature measurement with 9 measuring points with a set value specified by the user, including certificate	-	DL30-0109
Temperature measurement, 18 measuring points	Temperature measurement with 18 measuring points with a set value specified by the user, including certificate	-	DL30-0118
Temperature measurement, 27 measuring points	Temperature measurement with 27 measuring points with a set value specified by the user, including certificate	-	DL30-0127
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	-	DL10-0100
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0500

BINDER Best conditions for your success

-	DL20-0720
-	DL20-0720
-	
	DL20-0910
-	DL20-0810
-	DL20-0602
-	DL40-0100
-	DL44-0500
	DL50-0010
	-



NOTES

- 01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

BINDER GmbH

Tuttlingen, Germany TEL +49 7462 2005 0 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 asia@binder-world.com www.binder-world.com

BINDER Inc.

Bohemia, NY, USA TEL +1 631 224 4340 usa@binder-world.com www.binder-world.us

BINDER Environmental Testing

Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 china@binder-world.com www.binder-world.com

